



## Product data sheet REF 45.30.34

25.08.2026

| General data                                                                                                                                                                  |                                   |                                                            |                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|------------------------------------------------------------|----------------|
| article number                                                                                                                                                                | 45.30.34                          | Capsule for F.O Laryngoscope Handles, Brass LED, 2.0W 3.5V |                |
| Unit                                                                                                                                                                          | piece                             | Customs code (HS code)                                     | 90189084       |
| GMDN                                                                                                                                                                          | 60909                             | GTIN                                                       | 04046826534851 |
| Risk category                                                                                                                                                                 | N.A. (EU MDR)                     | UMDNS-Code                                                 |                |
| Classification                                                                                                                                                                | NA (EU MDR)                       | Base UDI-DI                                                |                |
| Net weight (kg)                                                                                                                                                               | 0,000                             | Operating instructions                                     |                |
| Latex free                                                                                                                                                                    | yes                               | Preparation instructions                                   |                |
| <div></div> |                                   |                                                            |                |
| Medicon media                                                                                                                                                                 |                                   |                                                            |                |
| Complete picture                                                                                                                                                              |                                   | Detail images                                              |                |
|                                                                                                                                                                               |                                   |                                                            |                |
| size                                                                                                                                                                          | 2.0W 3.5V                         | Coating                                                    |                |
| Storage conditions                                                                                                                                                            |                                   |                                                            |                |
| No special requirements                                                                                                                                                       |                                   |                                                            |                |
| Materials                                                                                                                                                                     |                                   |                                                            |                |
|                                                                                                                                                                               | Material number (DIN designation) |                                                            |                |
|                                                                                                                                                                               |                                   |                                                            |                |