



## Product data sheet REF 57.37.55

11.12.2025

| General data                                                                                                                                                                  |                                                                |                                                   |                         |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------|---------------------------------------------------|-------------------------|
| article number                                                                                                                                                                | 57.37.55                                                       | Caspar rong DieBlauen.2 15.5cm 2x12mm fenest serr |                         |
| Unit                                                                                                                                                                          | piece                                                          | Customs code (HS code)                            | 90189084                |
| GMDN                                                                                                                                                                          | 35541                                                          | GTIN                                              | 04046826449629          |
| Risk category                                                                                                                                                                 | 1r (EU MDR)                                                    | UMDNS-Code                                        | 15-669                  |
| Classification                                                                                                                                                                | 6 (EU MDR)                                                     | Base UDI-DI                                       | 4046826;B;R003;06;ai;5X |
| Net weight (kg)                                                                                                                                                               | 0,000                                                          | Operating instructions                            | GATDR00X                |
| Latex free                                                                                                                                                                    | yes                                                            | Preparation instructions                          | MPK20-2                 |
| <div></div> |                                                                |                                                   |                         |
| Medicon media                                                                                                                                                                 | 451.04.58 (Medicon DieBLAUEN.2 dism Rongeurs w Silicon Handle) |                                                   |                         |
| Complete picture                                                                                                                                                              |                                                                | Detail images                                     |                         |
|                                                                                             |                                                                |                                                   |                         |
| size                                                                                                                                                                          | 15.5cm 2x12mm                                                  | Coating                                           |                         |
| Storage conditions                                                                                                                                                            |                                                                |                                                   |                         |
| No special requirements                                                                                                                                                       |                                                                |                                                   |                         |
| Materials                                                                                                                                                                     |                                                                |                                                   |                         |
|                                                                                                                                                                               | Material number (DIN designation)                              |                                                   |                         |
| Main part                                                                                                                                                                     | 1.4021 (X20Cr13)                                               |                                                   |                         |
| Screw                                                                                                                                                                         | 1.4305 (X8CrNiS18-9)                                           |                                                   |                         |
| Handle                                                                                                                                                                        | ELASTOSIL LR3003 (Silikonkautschuk)                            |                                                   |                         |