



## Product data sheet REF 684.04.10

11.12.2025

| General data                                                                                  |                                              |                                                    |                                                                                              |
|-----------------------------------------------------------------------------------------------|----------------------------------------------|----------------------------------------------------|----------------------------------------------------------------------------------------------|
| article number                                                                                | 684.04.10                                    | Allis grasp fcps Ø 5mm rot double action w ratchet |                                                                                              |
| Unit                                                                                          | piece                                        | Customs code (HS code)                             | 90189084                                                                                     |
| GMDN                                                                                          | 33596                                        | GTIN                                               | 04046826307851                                                                               |
| Risk category                                                                                 | 2b (EU MDD)                                  | UMDNS-Code                                         | 11-502                                                                                       |
| Classification                                                                                | 9 (EU MDD)                                   | Base UDI-DI                                        |                                                                                              |
| Net weight (kg)                                                                               | 0,108                                        | Operating instructions                             | G6810101                                                                                     |
| Latex free                                                                                    | yes                                          | Preparation instructions                           | MPK04                                                                                        |
| <div></div>  |                                              |                                                    |                                                                                              |
| Medicon media                                                                                 |                                              |                                                    |                                                                                              |
| Complete picture                                                                              |                                              | Detail images                                      |                                                                                              |
| <div></div> |                                              |                                                    |                                                                                              |
| size                                                                                          | Ø 5mm                                        | Coating                                            | Artificially created galvanic gold layer (max 0.04mm) on parts of the surface of instruments |
|                                                                                               |                                              |                                                    |                                                                                              |
| Storage conditions                                                                            |                                              |                                                    |                                                                                              |
| No special requirements                                                                       |                                              |                                                    |                                                                                              |
| Materials                                                                                     |                                              |                                                    |                                                                                              |
|                                                                                               | Material number (DIN designation)            |                                                    |                                                                                              |
| Main part<br>Screw<br>Handle<br>Others                                                        | 1.4021 (X20Cr13)                             |                                                    |                                                                                              |
|                                                                                               | 1.4305 (X8CrNiS18-9)                         |                                                    |                                                                                              |
|                                                                                               | PA6.6GF30 (Polyamid mit 30% Glasfaseranteil) |                                                    |                                                                                              |
|                                                                                               | PPSU (Polyphenylsulfon)                      |                                                    |                                                                                              |